

Labino[®] Compact - White



COMPACT | CABLE | POWERFUL

MAKES IT BRIGHT

- Labino[®] Compact White lamps have a unique *white* luminance, which makes it possible to see things that have not been possible before.
- The Labino[®] Compact lamp contains the trigger ballast and the bulb in one housing, making it easy to handle and more flexible.
- The Labino[®] Compact lamp is available in three important distinctions – floodlight, midlight or spotlight – each giving different beams and intensities. The spotlight has the greatest focus and is the most intense, and the floodlight has the widest beam. The midlight is in between.
- The Labino[®] Compact obtains full power in 5-15 seconds and can be switched on and off whenever used, without pre-cooling.
- You can use the lamp outdoors, even in the rain, as the lamp is IP65 certified.
- Labino[®] Compact lamps are based on two key components – the Labino DL-35 W Gas Discharge Bulb (MPXL-technology) and the Labino Trigger Ballast (Electronics). The interface technology between these key components creates unbeatable output performance. Manufactured in Sweden.



135 WH (Mounting Brackets)



H135 WH (Top Handle)



PH135 WH (Pistol Handle)

TECHNICAL SPECIFICATION

Floodlight

Distribution angle: approx. 45°
Luminous flux: 3 500 lm

Midlight

Distribution angle: approx 20°
Luminous flux: 3 500 lm

Spotlight

Distribution angle: approx. 3.5°
Luminous flux: 3 500 lm
Intensity approx. 250 000 cd at 2500 mm

Voltage

- 100, 115 and 230 VAC
- Input Power: 43 W
- Output Power: 35 W

Weight

- Weight: 2.25 kilos (5 lbs)

Cables

- Cable length: 2 meters (2.2 yd)

Additional Information

- Mechanical Stability (bulb): IEC810
- Service life (bulb): approx. 5 000 hrs
- Start-up time: full power after 5-15 sec
- Material in housing: anodized aluminium, plastics PA6-30
- The housing is via pre milled slots prepared for mounting devices
- S, CE, ETL/cETL approved
- IP65 classified, dust and temporary water jetting proof



KE-TECH Kft.

1183 Budapest, Úllői út 470.
Tel.: (1) 290-0151, Fax: (1) 292-2159
E-mail: ketech@ketech.hu, www.ketech.hu

Labino AB shall not be held liable for any errors or omissions resulting from the test procedures that were used in validating performance of any Labino AB product nor for unforeseen errors or omissions in digital or printed material.